

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

- , - .

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

GP

00

P

LTR

DESCRIPTION

DATE

DWN

APVD



A2

REV PER ECR-15-007399

13MAY2015

ML


SZ



- 1 TO PREVENT THREAD STRIPPING, SCREW TORQUE SHOULD NOT EXCEED 9 IN LBS.
- 2 TAP HOLE IS 6-32UNC-2B, TWO MIN THREADS.
- 3 PACKAGED BULK.
- 4 HOUSING: THERMOPLASTIC
TAP: HIGH CONDUCTIVITY COPPER ALLOY
- 5 TAP: .000050 REF MATTE TIN OVER .000050 MATTE NICKEL BASED PLATING.
6. REFERENCE APPLICATION SPECIFICATION 114-11000 FOR DRILL HOLE SIZES AND FINISHES.

3	YES	YES	5055557-4
3	YES	NO	5055557-3
PACKAGING	HOUSING AND TAP ASSEMBLED	SCREW	PART NO.

.050 ± .005 DIA
REF



SECTION A-A
SCALE 10:1
10 PLACES

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. ALCORTA - 05-04-05 CHK A. FRANTUM 05-04-05 APVD S. FLICKINGER 05-04-05	Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC 108-11030	NAME POWER TAP CONNECTOR POWER DISTRIBUTION	
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .010 4 PLC ± - ANGLES ± -	APPLICATION SPEC 114-11000	SIZE A3	CAGE CODE 00779
MATERIAL 4	FINISH 5	WEIGHT -	DRAWING NO C-5055557	RESTRICTED TO -
CUSTOMER DRAWING			SCALE 4:1	SHEET 1 OF 1
			REV A2	