2-173977-4 ✔ ACTIVE


AMP CT


TE Internal #: 2-173977-4

Connector Assembly, Receptacle, Wire-to-Board, 4 Position, 2 mm [.079 in] Centerline, Insulation Displacement (IDC), 1 Row, Blue, Wire & Cable, AMP CT

View on TE.com >

Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings > AMP COMMON TERMINATION HOUSINGS







Connector Product Type: **Connector Assembly**

Connector & Housing Type: **Receptacle**

Connector System: **Wire-to-Board**

Number of Positions: **4**

Centerline (Pitch): **2 mm [.079 in]**

All AMP COMMON TERMINATION HOUSINGS (176)

Features

Housing Features

Housing Material	PBT GF
Centerline (Pitch)	2 mm[.079 in]

Product Type Features

Connector Product Type	Connector Assembly
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	4
Number of Rows	1

Body Features

Primary Product Color	Blue

Contact Features

Contact Current Rating (Max)	2 A

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)

Mechanical Attachment

Mating Retention	Without
Connector Mounting Type	Cable Mount (Free-Hanging)

Usage Conditions

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]

Operation/Application

Circuit Application	Power & Signal

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these

limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 2-292170-4
CT P/HDR ASSY 4P V W/O KINK T



TE Part # 2-292251-4
CT P/HDR BOX V 4P POL BLUE



TE Part # 2-292156-4
CT RELAY HDR ASSY FREE HANGING



TE Part # CAT-3983178-PHBXVD
CT 2mm Post Header Asmbly: Box V DIP




TE Part # 58372-1
HEAD (IDC) 2MM C.T. W/O TL



TE Part # CAT-3984552-BHTHVS
CT Box Header SMT: Vert, Shrouded



TE Part # 292254-4
CT RELAY HDR ASSY 4P NAT



TE Part # 2-292145-4
CT P/HDR ASSY V 4P W/O KINK BL




TE Part # 2-292157-4
CT RELAY W/COMMONING BAR 4P NA



TE Part # 2-292254-4
CT RELAY HDR ASSY 4P BLUE



TE Part # 2-173985-4
AMP CT MT AMP-IN HDR-V BLU 4P



TE Part # 2-292161-4
CT P/HDR ASSY V 4P W/KINK BLUE



TE Part # 58074-1
MTA 50/100/156 MANUAL TOOL FRAME



TE Part # 2-292164-4
CT P/HDR BOX H ASSY 4P T/P BLU




TE Part # 2-292165-4
CT P/HDR BOX V 4P T/P BLUE



TE Part # 5-292271-4
MT REC ASSY AU-PL. 4P BLUE



TE Part # 2-173983-4
AMP CT MT AMP-IN HDR-H YEL 4P



TE Part # CAT-AM7017-H342
AMP COMMON TERMINATION HEADERS



TE Part # CAT-3980407-RHDRRA
CT 2mm Header Assembly: Right Angle


Also in the Series | AMP CT




Connector Contacts(8)




Connector Hardware(46)



PCB Headers & Receptacles(756)



Wire-to-Board Connector Assemblies & Housings(255)



Wire-to-Board Headers & Receptacles (756)


Customers Also Bought



TE Part #179518-1
CT CRIMP-2 REC CONT. L/P



TE Part #CAT-AM7017-H8172
AMP COMMON TERMINATION HOUSINGS



TE Part #5-160432-4
250 FASTON REC 20-16 AWG TPBR



TE Part #3-353293-1
1.5MM CT MT REC ASSY 11P BLACK



TE Part #3-353293-5
1.5MM CT MT REC ASSY 15P BLACK



TE Part #3-353293-4
1.5MM CT MT REC ASSY 14P BLACK



TE Part #2-353293-8
1.5MM CT MT REC ASS'Y 8P BLACK



TE Part #1624204-2
23SE 1MA 6.35X50FL B7 CAT



TE Part #3-292216-2
MINI CT D/R RELAY 32P V NAT

Documents

CAD Files

Customer View Model

ENG_CVM_CVM_2-173977-4_M.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-173977-4_M.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-173977-4_M.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications

Application Specification

English

Instruction Sheets

MINI PRESS CT CONNECTOR (WAS IS-553J)

Japanese

Instruction Sheet (non U.S.)

Japanese

Agency Approvals

CSA Certificate

English

CSA Certificate

English