



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	CN INITIAL RELEASE	01/09/2024	BZHANG	WLI



2X RJ45 SHIELDED PLUG
GOLD PLATED CONTACTS
(8P8C)



PART NUMBER	LENGTH METERS[FEET]
TRD855SCRBLK-0.15M	0.15[0.49]
TRD855SCRBLK-0.5M	0.5[1.64]
TRD855SCRBLK-1M	1.0[3.28]
TRD855SCRBLK-1.5M	1.5[4.92]
TRD855SCRBLK-2M	2.0[6.56]
TRD855SCRBLK-2.5M	2.5[8.20]
TRD855SCRBLK-3M	3.0[9.84]
TRD855SCRBLK-5M	5.0[16.40]
TRD855SCRBLK-7M	7.0[22.97]
TRD855SCRBLK-10M	10.0[32.81]

NOTES

- 1.PLUG CONFORMS TO TIA-1096
- 2.OPERATING TEMPERATURE RANGE:-10°C TO +75°C
- 3.CABLE ASSEMBLY TO BE TESTED FOR CONTINUITY
- 4.CABLE ASSEMBLY TO BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13] THIRD-ANGLE PROJECTION 	APPROVALS	DATE	 an INFINITO brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY BZHANG	01/05/2024	
	CHECKED BY WLI	01/05/2024	
	APPROVED BY WLI	01/05/2024	
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	CATEGORY TELECOM/MODULAR		PRODUCT DESCRIPTION CA RJ45/RJ45 CAT5e SHLD PVC BLK
	SIZE A	CAGE CODE 43321	
	ITEM NO. TRD855SCRBLK-xxM	REV. A	
SCALE: NONE		CAD FILE: TRD855SCRBLK-xxM.SLDDRW	SHEET 1 OF 1