

Specification Sheet

Part Number: 157-00361



Offset design positions bundles away from obstructions, heat or sources of abrasion.

Low profile head allows mounts to stack, providing more mounting versatility from a single stud.

Four-pawl, three-tooth design delivers outstanding stud retention to keep bundles secure.

PA46 material option allows use in high-heat applications.

Offset Low-Profile M8 Stud Mount Tie, 7.5" Tie, 25.5 mm Offset, 50lb Tensile Strength, PA46, Brown, 2000/pkg

Article Number 157-00361

Type T50ROSLPM8SMSO25

Color Brown (BN)

Quantity Per carton

Product Description

This mount's offset design positions bundles away from obstructions, heat or sources of abrasion. It features a low-profile head, allowing multiple tie mounts to be stacked on a single bolt and providing space savings in tight areas. With their low insertion force and high extraction performance, HellermannTyton mounting ties offer the ideal combination of high-grade materials and superior design to suit the mounting and bundling needs of complex applications. Available in standard and high-heat material options.

Short Description	Offset Low-Profile M8 Stud Mount Tie, 7.5" Tie, 25.5 mm Offset, 50lb Tensile Strength, PA46, Brown, 2000/pkg
Global Part Name	T50ROSLPM8SMSO25-PA46-BN
Minimum Tensile Strength (Imperial)	50.0
Minimum Tensile Strength (Metric)	223.0
Length L (Imperial)	8.9
Length L (Metric)	226.14
Offset Length (Imperial)	1.0
Offset Length (Metric)	25.5
Fixation Method	Stud Mount
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Width W (Imperial)	0.70
Width W (Metric)	17.75
Bundle Diameter Min (Imperial)	0.08
Bundle Diameter Min (Metric)	2.0

Bundle Diameter Max (Imperial)	1.97
Bundle Diameter Max (Metric)	50.0
Cable Ties	157-00361
Height H (Imperial)	0.25
Height H (Metric)	6.30
Mounting Hole Diameter D (Imperial)	0.31" x 0.05
Mounting Hole Diameter D (Metric)	M8 x 1.25
Stud Diameter (Metric)	8.0 mm
Stud Diameter (Imperial)	0.31
Material	Polyamide 4.6 (PA46)
Material Shortcut	PA46
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +266°F (-40°C to +130°C)

Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	2000
Package Quantity (Metric)	2000
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)