





REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



技术参数:

PIN数: 2~12

适用线规: AWG22#~18#

适用基板厚度: 1.6mm

温度范围: -25℃~85℃

额定电压: 250V AC/DC

额定电流: 7.5A


接触电阻: $\leq 0.015 \Omega$

绝缘电阻: $\geq 1000N \Omega$

耐压: 1500V AC/minute

材料: (Nylon)66UL94V-2(0)

Part No	Pin	A	B
CVHR-2N-JK	2	3.96	8.07
CVHR-3N-JK	3	7.92	12.03
CVHR-4N-JK	4	11.88	15.99
CVHR-5N-JK	5	15.84	19.95
CVHR-6N-JK	6	19.8	23.91
CVHR-7N-JK	7	23.76	27.87
CVHR-8N-JK	8	27.72	31.83
CVHR-9N-JK	9	31.68	35.79
CVHR-10N-JK	10	35.64	39.75
CVHR-11N-JK	11	39.6	43.71
CVHR-12N-JK	12	43.58	47.67

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.X	± 0.35	X.*	$\pm 5^{\circ}$	PART NO.	TITLE:
.XX	± 0.25	X.X*	$\pm 3^{\circ}$	CVHR-XN-JK	VH3.96MM HOUSING
.XXX	± 0.15	X.XX*	$\pm 1^{\circ}$	DESIGN: Ethan	MANUFACTURE DWG
UNITS	mm				
MATERILA	---	CHED: Olvia			
FINISH	---	APPD: Ava			
					SCALE N:A SHEET 1/1