



REV.	ECN NO.	REVISED	DATE

NOTE:

- MATERIAL:
  - HOUSING: PA66 BLACK
  - CONTACT: SUS304 T=0.4MM  
(SURFACE PLATING: Ni-PLATING)  
SEE ORDERING INFORMATION
- ELECTRIC:
  - DIELECTRIC VOLTAGE: 500V AC ONE MINUTE
  - OPERATING TEMPERATURE: -10°C ~ +80°C

ORDERING INFORMATION

**BH-18650-A1BJ036**

电池盒





电池型号

DIP 90° TYPE


PLATING:  
A-Au-PLATING  
J-Ni-PLATING  
K-Sn-PLATING

MATERIAL:  
1B-PA66 BLACK

工程部  
2025-04-24  
H. WANG



SECTION VIEW A-A



PCB Layout Diagram  
TOP View

UNLESS OTHERWISE SPECIFIED TOLERANCES		<b>MYOUNG 美用</b> <a href="http://www.meiyangdz.com">www.meiyangdz.com</a>	
DECIMALS: X :±0.30 X.X :±0.25 X.XX :±0.20 X.XXX :±0.10	ANGLES: X :±1° X.X :±0.5°	DSND WangHeng	DATE 2025-04-24
WEIGHT:		CHKD ZhouRuicai	DATE 2025-04-24
SHEET 1 OF 1		APVD XueShunyong	DATE 2025-04-24
TITLE:		PART NO.:	
		BH-18650-4J Ni DIP PA66 并联	
		SCALE: 1:1	SIZE: A4
		VIEW:	
		UNIT: mm	REV.: A/0
		OBJECT: MY	DRAW NO.: WD-CP-0475

2	TERMINAL	8	SUS304, T=0.4MM	Ni-Plating
1	HOUSING	1	PA66	BLACK
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR