




序号	品名	材质
1	1.0嵌芯(H2.5)	LCP UL94V-0 本色
2	1.0下接端子(H2.5)	铜合金/表面镀锡
3	1.0卧式后盖(H2.5)	LCP UL94V-0 黑色
4	1.0卧式焊片(H2.5)	铜合金/表面镀锡

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: -25°C~+85°C.
3. 额定电压: 50V, AC/DC.
4. 接触电阻:  $\leq 0.03\Omega$ .
5. 绝缘电阻:  $\geq 500M\Omega$

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD					
DIM. TOL. .x ±0.30 .xx ±0.20 .xxx ±0.05 GENERAL ANGLE: .x ±5° .xx ±2° .xxx ±1°		TITLE: 1.0 Pitch H2.5 ZIF R/A Type Under CONN					
		DWG. NO.: FPC-07 -SX-FCA		CHECKED: MAX			
		PART NO.: FPC-07 -SX-FCA		DRAWN: ELLA			
UNIT: mm		SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn		