


序号	品名	材质
1	XH2.5 胶芯	PA66 UL94V-2 Red
2	XH2.5 弯针 端子	Copper Alloy/ Tin Plating



Part No	Pin	A	B
BX-HA2.54-2PWZ-R	2	2.5	7.5
BX-HA2.54-3PWZ-R	3	5.0	10.0
BX-HA2.54-4PWZ-R	4	7.5	12.5
BX-HA2.54-5PWZ-R	5	10.0	15.0
BX-HA2.54-6PWZ-R	6	12.5	17.5
BX-HA2.54-7PWZ-R	7	15.0	20.0
BX-HA2.54-8PWZ-R	8	17.5	22.5
BX-HA2.54-9PWZ-R	9	20.0	25.0
BX-HA2.54-10PWZ-R	10	22.5	27.5
BX-HA2.54-11PWZ-R	11	25.0	30.0
BX-HA2.54-12PWZ-R	12	27.5	32.5
BX-HA2.54-13PWZ-R	13	30.0	35.0
BX-HA2.54-14PWZ-R	14	32.5	37.5
BX-HA2.54-15PWZ-R	15	35.0	40.0
BX-HA2.54-16PWZ-R	16	37.5	42.5
BX-HA2.54-17PWZ-R	17	40.0	45.0

Technical Index:

1. Temperature range: -25°C~85°C.
2. Rated voltage: 250V
3. Rated current: 3.0A.
4. Contact resistance: ≤20mΩ.
5. Withstanding voltage: 1000V AC/minute.
6. Insulation resistance: ≥1000MΩ.

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA		料号 PART NO.	BX-HA2.54-NPWZ-R	版本 REV.	A
			X.±0.50	X°.±5°	审核 CHECK	EVA		品名 TITLE	HA2.5 弯针带加	页次 SHEET	1/1
			.X±0.20	X.X°:±3°	核准 APPROVAL	JADE		客户料号 CUTM.NO.		<b>Bossie (博锡)</b>	
			.XX±0.10	X.XX°:±1°	单位 UNITS	MM	比例 SCALE	1:1			