

0395



Basic Part Number	Board Thickness	Length V
0395-1	.031	.062
0395-2	.062	.094
0395-3	.094	.125
0395-4	.125	.156
0395-5	.188	.219


0395-X-15-XX-07-XX-10-0
Swage mount in .096 hole

8001




8001-0-19-XX-07-XX-10-0
Wire Termination

8016




8016-0-15-XX-07-XX-10-0
Press-fit in .131 mounting hole

0350



0350-0-15-XX-07-XX-10-0
Hex press-fit in .129±.002
plated thru hole

8837



8837-0-15-XX-14-XX-10-0
Solder mount in .159 min.
mounting hole

SPECIFICATIONS

SHELL MATERIAL:
Brass Alloy 360, 1/2 Hard

CONTACT MATERIAL:
Beryllium Copper Alloy 172, HT

DIMENSION IN INCHES
TOLERANCES ON:
LENGTHS: ±.005
DIAMETERS: ±.002
ANGLES: ± 2°

ORDER CODE: XXXX - X - 15 - XX - XX - XX - 10 - 0

BASIC PART #

SPECIFY SHELL FINISH:
01 200µ" TIN/LEAD OVER NICKEL
80 200µ" TIN OVER NICKEL ◇
15 10µ" GOLD OVER NICKEL ◇

SPECIFY CONTACT FINISH:
01 200µ" TIN/LEAD OVER NICKEL
80 200µ" TIN OVER NICKEL ◇
27 30µ" GOLD OVER NICKEL ◇

RoHS 2002/95/EC

SELECT CONTACT
#07 or #14 CONTACT (DATA ON PAGE 214 & 215)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

8001-0-19-80-07-80-10-0 8001-0-19-01-07-27-10-0 8001-0-19-01-07-01-10-0 8001-0-19-80-07-27-10-0 8001-0-19-15-07-27-10-0