

Rev	AWO #	Description	Date	Appr
-		RELEASED	8/16/21	

APPROVED: _____


DATE: _____ TITLE: _____





MMI-M0RSXXXS-IP68

- SIZE 0
- CODING
  - 1 = CODE 1
  - 2 = CODE 2
  - 3 = CODE 3
- # OF POSITIONS
  02, 03, 04, 05, & 07



Panel Cut-Out
(Rear Panel Mounting)

CODING OPTIONS



CODE 1 | CODE 2 | CODE 3

	2 Pin	3 Pin	4 Pin	5 Pin	7 Pin
Configuration					
Diameter of Pin	ø0.9	ø0.9	ø0.7	ø0.7	ø0.5
Testing Voltage	1200V	1200V	1000V	1000V	800V
Working Voltage	250V	250V	200V	200V	200V
Rated Current / Pin	8A	7A	5A	5A	2A

SPECIFICATIONS:
Material:
Body: Brass, Natural Chrome Plated
Insulator: PPS, color Beige
Terminal: Brass, Gold Plated
O-Ring: Silicone
Electrical:
Voltage Rating: See chart
Current Rating: See chart
Dielectric withstanding voltage: See chart
Electrical Life: 1,000 Cycles min.
Mechanical:
Endurance: 5,000 Cycles Min.
Temperature Rating:
Operating temperature: -55°C to +150°C
Environmental:
IP68 Protection (Panel and Mated Condition)
Lead free, RoHS compliant

RoHS COMPLIANT

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

APPROVALS		DATE
DRAWN	SS	8/16/21
CHECKED	SS	8/16/21
APPROVED		

ADAM TECH
909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE: PUSH-PULL SOCKET, VERTICAL, SIZE 0, METAL BODY, FRONT PANEL MOUNT, SOLDER TERMINAL, IP68

SIZE	PART NO.	REV.
X	MMI-M0RSXXXS-IP68	-

REF: SXXXXXX | SCALE: NTS | SHEET 1 OF 1