293315-2 × OBSOLETE

NECTOR | NECTOR S

TE Internal #: 293315-2

TE Internal Description: NECTOR S PCB CONN. ASSY 90 DEG OUTLET

View on TE.com >







Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked.Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles'(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Also in the Series | NECTOR S



Insertion & Extraction Tools(3)



Plug & Socket Lighting Connector Accessories(42)



Plug & Socket Lighting Connectors(30)

Customers Also Bought



TE Part #1-2379237-1
NECTOR T, INLINE SOCKET, SCREW, Key-A,S2



TE Part #2-32510-1
TERMINAL,PIDG SPD FLG 12-10 8



TE Part #1-2379238-1
NECTOR T, INLINE PIN, SCREW, Key-A, S2



TE Part #1803337-2
ANVIL, COMBINATION



TE Part #2-1803002-6
ANVIL



TE Part #2150719-1
OCEAN_2.0_Applicator-E-180F-REM



TE Part #2266508-2
OCEAN_2.0_Applicator-S-070F120OA-RSA



TE Part #3-1633919-6
ANVIL COMBINATION



TE Part #7-2834182-2
1P,PLUG CABLE ASSY-203.2MM, WHITE,TIN



TE Part #1586378-1
03P UMNL CAP HSG NATL

Documents

Product Drawings

NECTOR S PCB CONN. ASSY 90 DEG OUTLET

English

CAD Files

Customer View Model

ENG_CVM_CVM_293315-2_F.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_293315-2_F.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_293315-2_F.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

NECTOR_S_LINE_CONNECTOR_BROCHURE

English

Product Specifications

Application Specification

English