


REV.	DESCRIPTION	ECN NO.	NAME	DATE

NOTES:
 1.HUOSING:LCP HGH-TEMP THERMOPLASTIC UL94V-0
 2.TERMINAL:PHOSPHOR BRONZE
 3.COLOR:BEIGE



SOCKET H1	PLUG H			
	4.70	5.70	6.70	7.70
3.70	5.00	6.00	7.00	8.00
7.70	9.00	10.00	11.00	12.00
11.70	13.00	14.00	15.00	16.00
15.70	17.00	18.00	19.00	20.00

Model	PIN	DIM A	DIM B	DIM C	DIM D	DIM E	DIM F
B0801FSV50-40P	40	21.80	15.20	16.80	20.20	18.80	20.15
B0801FSV50-50P	50	25.80	19.20	20.80	24.20	22.80	24.15
B0801FSV50-60P	60	29.80	23.20	24.80	28.20	26.80	28.15
B0801FSV50-80P	80	37.80	31.20	32.80	36.20	34.80	36.15
B0801FSV50-100P	100	45.80	39.20	40.80	44.20	42.80	44.15
B0801FSV50-120P	120	53.80	47.20	48.80	52.20	50.80	52.15
B0801FSV50-140P	140	61.80	55.20	56.80	60.20	58.80	60.15
B0801FSV50-160P	160	69.80	63.20	64.80	68.20	66.80	68.15
B0801FSV50-180P	180	77.80	71.20	72.80	76.20	74.80	76.15
B0801FSV50-200P	200	85.80	79.20	80.80	84.20	82.80	84.15

GENERAL TOLERANCE	DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD				
DIM. x. ±0.25 x.x ±0.20 x.xx ±0.10 GENERAL ANGLE: x.' ±1' x.X' ±	TITLE: 0.8mm PITCH BTB CONNECTOR SOCKET				
	DWG. NO.: B0801FSV50-XP		CHECKED: MAX		
	PART NO.: B0801FSV50-XP		DRAWN: ELLA		
	UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxcn
	APPROVED: WILL				

BXCONN[®]

