ATGBICS

ATGBICS MPO Female-Female 8 Fibres OM4 50/125 Multimode Trunk Cable, Type B, LSZH 2.0, 5m

Brand : ATGBICS

Product code: TCAB-8MPOFF-OM4-5M

Product name : ATGBICS MPO Female-Female 8 Fibres OM4 50/125 Multimode Trunk Cable, Type B, LSZH 2.0, 5m



ATGBICS MPO Female-Female 8 Fibres OM4 50/125 Multimode Trunk Cable, Type B, LSZH 3.0, 5m

ATGBICS MPO Female-Female 8 Fibres OM4 50/125 Multimode Trunk Cable, Type B, LSZH 2.0, 5m:

This product is high quality MPO Trunk Cable providing the backbone for Data Centre cabling. Due to its 3mm diameter they are space saving, ease cable management problems and optimise the Data Centre airflow. This is an OM4 8-fibre cable over multimode, used for 40G QSFP+ SR4/CSR4 or QSFP28 100G SR4 direct connection and high-density data centre applications. The MPO connection interface has been defined within the IEC-61754-7 international standards. Our products are rigorously tested and we proudly offer a compatibility guarantee and lifetime warranty.
ATGBICS MPO Female-Female 8 Fibres OM4 50/125 Multimode Trunk Cable, Type B, LSZH 2.0, 5m. Cable length: 5 m, Fibre optic type: OM4, Connector 1: MPO, Connector 2: MPO, Core diameter: 50 µm

Features	
Cable length *	5 m
Connector 1 *	MPO
Connector 2 *	MPO
Connector 1 gender *	Female
Connector 2 gender *	Female
Fibre optic type *	OM4
Product colour *	Violet
Full duplex	✗
Core diameter	50 µm
Cladding diameter	125 µm
Fiber mode structure	Multi-mode
Wavelengths supported	850,1300 nm
Ethernet interface type	40 Gigabit Ethernet, 100 Gigabit Ethernet

Features	
Insertion loss	0.35 dB
Return loss	50 dB
Jacket material *	Low smoke zero halogen (LSZH)
Polarity	B
Country of origin	China
Technical details	
Sustainability certificates	RoHS
Doesn't contain	Halogen
Operational conditions	
Operating temperature (T-T)	-10 - 70 °C
Storage temperature (T-T)	-40 - 85 °C
Packaging data	
Quantity per pack	1 pc(s)



5056468745767

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 21-SEP-2023. Prints or copies of Information are only valid on the printed Publication date