



A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE



COMMON TOLERANCE	
X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT	MM	PROJECTED	
DRAWN BY	FUYUAN	CHECKED BY	COCO
DATE	2019	APPROVAL	B ALEN
<b>ROCPCU TECHNOLOGY CO.,LTD</b>			

PRODUCT NAME:	
MODEL NO:	TP91603P224RA
Https:	www.rocpcu.tw
<small>Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission</small>	



A	B	C	D	E	F	G		
<b>材质参数</b>								
10	luminous zone 发光区	PC 塑料	1					
9	LEDpin LED脚	Brass 黄铜	1		Silvering 镀银			
8	Base 底座	PA46	1					
7	Pin 引脚	Brass 黄铜	1		gold-plating 镀金			
6	Contact material 接触材质	silver alloy 银合金	1					
5	LED Base LED基座	PBT	1					
4	Arm nut 固定螺帽	Brass 黄铜	1		nickeling 镀镍			
3	Oring O型圈	Silica gel 硅胶	1					
2	Housing 外壳	Aluminum alloy 铝合金	1		Oxidized/Black 氧化/黑色			
1	Key 按键	Aluminum alloy 铝合金	1		Oxidized/Black 氧化/黑色			
NO 序号	Part name 部件名	Material 材料	QTY 数量		Remark 备注			
A4				UNIT	MM	PROJECTED		PRODUCT NAME:
A3				DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91603P224RA
A2				DATE	2019	APPROVAL B	ALEN	Https: www.rocpu.tw
A1				<b>ROCPU TECHNOLOGY CO.,LTD</b>				
REV	DATE	REVISION	DESCRIPTION	ISSUE	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission			



COMMON TOLERANCE

X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission