








ROHS Compliant

MAPX	MODIFICATION	DATE	DRAW	APPROVE

序号	品名	材质
1	0.5 Pitch 掀盖卧式带扣胶芯(H=2.0)	LCP UL94V-0 本色
2	0.5 Pitch 掀盖卧式带扣后盖(H=2.0)	LCP UL94V-0 黑色
3	0.5 Pitch 掀盖卧式带扣端子(H=2.0)	铜合金/表面镀金
4	0.5 Pitch 掀盖卧式带扣焊片(H=2.0)	铜合金/表面镀锡



P/N	PIN	DIM A	DIM B	DIM C	DIM D	DIM E	DIM F
FPC-0.5FXS-4PWBR-H20	4	6.30	2.57	1.50	0.70	4.10	4.10
FPC-0.5FXS-5PWBR-H20	5	6.80	3.07	2.00	5.20	4.60	4.60
FPC-0.5FXS-6PWBR-H20	6	7.30	3.57	2.50	5.70	5.10	5.10
FPC-0.5FXS-7PWBR-H20	7	7.80	4.07	3.00	6.20	5.60	5.60
FPC-0.5FXS-8PWBR-H20	8	8.30	4.57	3.50	6.70	6.10	6.10
FPC-0.5FXS-9PWBR-H20	9	8.80	5.07	4.00	7.20	6.60	6.60
FPC-0.5FXS-10PWBR-H20	10	9.30	5.57	4.50	7.70	7.10	7.10
FPC-0.5FXS-11PWBR-H20	11	9.80	6.07	5.00	8.20	7.60	7.60
FPC-0.5FXS-12PWBR-H20	12	10.30	6.57	5.50	8.70	8.10	8.10
FPC-0.5FXS-13PWBR-H20	13	10.80	7.07	6.00	9.20	8.60	8.60
FPC-0.5FXS-14PWBR-H20	14	11.30	7.57	6.50	9.70	9.10	9.10
FPC-0.5FXS-15PWBR-H20	15	11.80	8.07	7.00	10.20	9.60	9.60
.....							
FPC-0.5FXS-76PWBR-H20	76	42.30	51.00	37.50	40.70	40.10	40.10
FPC-0.5FXS-77PWBR-H20	77	42.80	51.50	38.00	41.20	40.60	40.60
FPC-0.5FXS-78PWBR-H20	78	43.30	52.00	38.50	41.70	41.10	41.10
FPC-0.5FXS-79PWBR-H20	79	43.80	52.50	39.00	42.20	41.60	41.60
FPC-0.5FXS-80PWBR-H20	80	44.30	53.00	39.50	42.70	42.10	42.10

技术指标:

1. 塑件表面应光洁, 无毛边, 无明显收缩、缺陷、裂纹等现象.
2. 温度范围: $-40^{\circ}\text{C} \sim 105^{\circ}\text{C}$.
3. 额定电流: 0.5A
4. 额定电压: 50V, AC.
5. 接触电阻: $50\text{m}\Omega$ MAX.
6. 绝缘电阻: $500\text{M}\Omega$ Min.
7. 耐电压: 150V AC/1Minute

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co., Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			
DECIMALS:	ANGLES:	TITLE: 0.5 Pitch 掀盖卧式带扣(H=2.0)	
.X:±0.50	±1°	PAR	FPC-0.5FXS-NPWBR-H20
.X:±0.20		DWN	Lucas
.XX:±0.10		CHKD	Ethan
.XXX:±0.05		APVD	Jacob
CUSTOMER COPY		SCALE 1:1	UNIT:MM
		SIZE:A4	SHEET:1F1
			REV:A