


性能:

- 额定电流: 5.0A
- 额定电压: 30V
- 耐电压: 500V
- 接触电阻: 30mΩ MAX
- 绝缘电阻: 500MΩ
- 工作温度: -55℃~+125℃
- 塑件(材质): LCP黑色
- 接触点(材质): 黄铜C2680, 接触面镀金3U"
焊脚镀金1U"



RECOMMENDED PCB LAYOUT
TOP VIEW (.XX±0.05)

| 规格型号 | DIM A | DIM B |
|--------------------|-------|-------|
| HYCW-BF2P3016D-30 | 6.0 | 3.0 |
| HYCW-BF3P3016D-60 | 9.0 | 6.0 |
| HYCW-BF4P3016D-90 | 12.0 | 9.0 |
| HYCW-BF5P3016D-120 | 15.0 | 12.0 |
| HYCW-BF6P3016D-150 | 18.0 | 15.0 |
| HYCW-BF7P3016D-180 | 21.0 | 18.0 |
| HYCW-BF8P3016D-210 | 24.0 | 21.0 |



深圳市华宇创精密电子有限公司

| | | | | |
|--|--------------------|----------------------|-------------------------------|----------------|
| TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2' X.X' ±0.5' UNIT: mm [inch] SCALE:1:1 SIZE: A4 | DRAWN BY : 陈一鸣 | DATE : 2014-02-23 | PART NAME: 3.0PH 1.6H 母座有柱 | |
| | CHECKED BY: 马跃 | DATE : 2014-02-23 | PART NO. | SEE TABLE |
| | APPROVED BY: 邱敏 | DATE : 2014-02-23 | DRAW NO: | HYC-2604131057 |
| | | | SHEET NO. | 1 OF 1 |