


NOTES:







- 1.Circuit: ON/OFF
- 2.Operation force: 500±200gf
- 3.Electrocal rating: 10(4)A 250V~ VDE
10A 125V~ UL CUL CQC
6A 250V~ UL CUL CQC
- 4.Contact resistance: <50mΩ
- 5.Insulation resistance: >100MΩ (500VDC
between open contacts)
- 6.Dielectric strength: >1500VAC 0.5mA 1 minute
- 7.Color: cover is dark red, body is black

Panel cut - out:

X	Dim.Y	Dim.Z
0.75~1.25mm	19.20+0.1/-0	12.80+0.1/-0
1.25~2.0mm	19.30+0.1/-0	12.80+0.1/-0



Circuit of Switch



NO	DESCRIPTION	NO	DESCRIPTION	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN		MM	
				RANGE	TOLERANCE					SCALE	FIT		
5	→	10	→	X	±0.4	ROCK TEK ELECTRICAL(SHENZHEN) CO.,LTD.			LMC 2018.04.19	MATERIAL NO.		DRAWING NO.	REV
4	→	9	→	X.X	±0.3					RT-S01-113-L2NBRIA			
3	→	8	→	X.XX	±0.2								
2	→	7	→	ANGLES	±0.5°								
1	→	6	→										