





D

C

B

A



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—




FOR 5-1734100-4 WITH CAP

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN F. YANG 31MAR2009	TE Connectivity Ltd.			
DIMENSIONS: mm		CHK S. CHIEN 31MAR2009				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD W. KODAMA 31MAR2009	NAME			
0 PLC $\pm -$ 1 PLC $\pm -$ 2 PLC $\pm -$ 3 PLC $\pm -$ 4 PLC $\pm -$ ANGLES $\pm -$		PRODUCT SPEC 108-57876 APPLICATION SPEC —	PLUG ASSEMBLY, VERTICAL BOARD-TO-BOARD, CHAMP .050, SERIES I			
MATERIAL SEE NOTE		FINISH SEE NOTE	SIZE A3	CAGE CODE 00779	DRAWING NO C-1734100	RESTRICTED TO —
CUSTOMER DRAWING		SCALE —	SHEET 2 of 6	REV E1		

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



VERTICAL PLUG ASSEMBLY MATED TO VERTICAL RECEPTACLE ASSEMBLY



VERTICAL PLUG ASSEMBLY MATED TO RIGHT ANGLE RECEPTACLE ASSEMBLY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	-	TE Connectivity Ltd.		
		CHK	-			
		APVD	-	NAME		
		PRODUCT SPEC	-	PLUG ASSEMBLY, VERTICAL BOARD-TO-BOARD, CHAMP .050, SERIES I		
		APPLICATION SPEC	-			
		WEIGHT	-	SIZE	CAGE CODE	DRAWING NO
				A3	00779	C-1734100
		CUSTOMER DRAWING		SCALE	SHEET	REV
				-	3 of 6	E1

D

C

B

A



D

C

B

A

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—



D2	OBSOLETE	4.88	3.42	54	8	432	5-1734100-2	120
							3-1734100-2	
							1-1734100-2	
							5-1734100-0	100
	7.70	5.58	54	16	864	3-1734100-0		
						1-1734100-0		
							4-1734100-9	80
	5.28	3.80	54	16	864	2-1734100-9		
						1734100-9		
	5.38	3.90				4-1734100-8		
		2-1734100-8						
						1734100-8	68	
4.76	3.37	54	16	864	4-1734100-7			
					2-1734100-7			
						1734100-7	60	
4.36	3.11	54	16	864	4-1734100-6			
					2-1734100-6			
						1734100-6	50	
D2	OBSOLETE	5.72	4.08	54	24	1296		5-1734100-9
								3-1734100-9
								1-1734100-9
	5.70	4.07	4-1734100-5					
						2-1734100-5		
						1734100-5	40	
4.77	3.50	54	24	1296	4-1734100-4			
					2-1734100-4			
						1734100-4	30	
4.46	3.03	54	24	1296	4-1734100-3			
					2-1734100-3			
						1734100-3		
		G.W./CARTON	N.W./CARTON	PCS/TUBE	TUBES/CARTON	QUANTITY/CARTON (PCS)	PART NUMBER	PDS.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± —
1 PLC ± —
2 PLC ± —
3 PLC ± —
4 PLC ± —
ANGLES ± —
FINISH

DWN —
CHK —
APVD —
PRODUCT SPEC —
APPLICATION SPEC —
WEIGHT —

TE Connectivity Ltd.

PLUG ASSEMBLY, VERTICAL
BOARD-TO-BOARD,
CHAMP .050, SERIES I

SIZE A3CAGE CODE 00779DRAWING NO C-1734100RESTRICTED TO —

CUSTOMER DRAWINGSCALE —SHEET 4 of 6REV E1

1470-19 (1/15)

D

C

B

A


D

C

B

A

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—



D2 OBSOLETE						5-1734100-8	180
	2.85	1.97	16	10	160	3-1734100-8	
						1-1734100-8	
	2.62	1.73	16	10	160	5-1734100-6	160
						3-1734100-6	
						1-1734100-6	
G.W./CARTON (KG)		N.W./CARTON (KG)	PCS/TRAY	TRAYS/CARTON	QUANTITY/CARTON (PCS)	PART NUMBER	POS.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± —
1 PLC ± —
2 PLC ± —
3 PLC ± —
4 PLC ± —
ANGLES ± —
FINISH

DWN —
CHK —
APVD —
PRODUCT SPEC —
APPLICATION SPEC —
WEIGHT —

TE Connectivity Ltd.

PLUG ASSEMBLY, VERTICAL
BOARD-TO-BOARD,
CHAMP .050, SERIES I

SIZE A3CAGE CODE 00779DRAWING NO C-1734100RESTRICTED TO —

CUSTOMER DRAWINGSCALE —SHEET 5 of 6REV E1

