




Part Number : [150160651](#)

Product Description : 0.50mm Pitch Premo-Flex One-Touch FFC Jumper with Ears, Same Side Contacts (Type A), 102.00mm Cable Length, Gold (Au) Plating, 60 Circuits

Series Number : 15016

Status : Active

Product Category : Flat-Flexible Cable (FFC)



Documents & Resources

Drawings


[150160651_sd.pdf](#)

Specifications

[150160001-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 33
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	Flat-Flexible Cable (FFC)
Series	15016
Description	0.50mm Pitch Premo-Flex One-Touch FFC Jumper with Ears, Same Side Contacts (Type A), 102.00mm Cable Length, Gold (Au) Plating, 60 Circuits
Product Name	Premo-Flex FFC Jumper
UPC	195842135161

Electrical

Current - Maximum per Contact	0.4A
Voltage - Maximum	N/A

Physical

Cable Length	102.00mm
Circuits (Loaded)	60
Contact Layout Type	A (same side)
Design Feature	Superior Retention
Material - Plating Mating	Gold
Packaging Type	Bag
Pitch - Mating Interface	0.50mm
Temperature Range - Operating	-40° to +105°C
Termination Style	FFC Connector
Wire/Cable Type	Flat Flex Cable
Wire Size (AWG)	N/A

Mates With / Use With

Mates with Part(s)

Description	Part Number
Easy-On FFC/FPC One-Touch Connector, 0.50mm Pitch, Right-Angle, Bottom Contact, 4.46mm Height, 105°C Operating Temperature, 60 Circuits, Gold (Au) Plating	<u>2004850460</u>
Easy-On FFC/FPC One-Touch Connector, 0.50mm Pitch, Vertical, 5.60mm Height, 105°C Operating Temperature, 60 Circuits, Gold (Au) Plating	<u>2004850560</u>

This document was generated on Jan 21, 2025