








- NOTES:
1. MATERIAL:
 - 1.1. HOUSING: PPA,COLOR IS BLACK;
 - 1.2. CONTACT: PHOSPHOR COPPER ;
 2. FINISH:
 - 2.1. TERMINAL:
CONTACT AREA: NI PLATED OVER ALL;
SOLDER AREA: SN PLATED OVER ALL;
 3. ELECTRICAL:
 - 3.1. VOLTAGE RATING: 30 VAC RMS;
 - 3.2. CURRENT RATING: 0.5 AMP;
 - 3.3. CONTACT RESISTANCE: 30MILLIOHMS MAX.;
 - 3.4. WITHSTAND VOLTAGE: 500 VAC RMS
50(60)Hz,1MIN.;
 - 3.5. INSULATION RESISTANCE: 100MEGOHMS MIN
@500V DC;
 4. MECHANICAL:
 - 4.1. MATING FORCE: 5~25N;
 - 4.2. UNMATING FORCE: 5~25N;
 - 4.3. OPERATING LIFE: 5000 CYCLES;
 5. ENVIRONMENTAL:
 - 5.1. STORAGE TEMPERATURE RANGE: -40°C~+85°C;
 - 5.2. OPERATION TEMPERATURE RANGE: -25°C~+70°C;
 - 6.SALT SPRAY TEST:8H(EXCLUDING RIVETED BENDS)



序号	品名	材质	电镀/颜色	备注
A	基座	PPA	黑色	
B	端子	磷铜0.25T	镀银	

			GENERAL TOLERANCE		制图	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	审核				
			X.X	±0.30	批准	产品名称	320A 3.5耳机插座 插件	版本	A
			X.XX	±0.20	APPROVAL	TITLE		REV.	
			X.XXX	±0.10	比例	产品料号	HC-PJ-320A-3P-D	单位	mm
			Angle	±3.0°	SCALE	PART NO.		页次	1/1
序号	变更内容	日期			投影	材料			
No.	MODIFY CONTENT	MODIFY DATE			Projection	MATERIAL			