



产品编号 : 194390005

Product Description : Loxon Locking Quick Disconnect, Female, for 10-12 Wire, Reel, Tab 6.35 x 0.81mm

系列号 : 19439

状态 : Active

Product Category : Quick Disconnects

工程编号 : CZ-4152



文件和资源

图纸

[图纸 194390005_sd.pdf](#)

[包装设计图 194390009-000.pdf](#)

产物环境合规

合规

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Not Reviewed per EU 2015/863

多部分产品合规性声明

- Eu RoHS
- REACH SVHC
- Low-Halogen

多部分行业合规性文件

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

产品详情

常规

状态	活动
类别	Quick Disconnects
系列	19439
说明	Loxon Locking Quick Disconnect, Female, for 10-12 Wire, Reel, Tab 6.35 x 0.81mm
产品系列	Standard Quick-Disconnect Terminals
产品名称	Loxon
类型	Quick Disconnect
UPC	193264611676

机构

UL	E79133
----	--------

电气

电压 - 最大	600V AC
---------	---------

物理

筒型	已关闭
性别	女
符合灼热丝规范	否
绝缘	否
绝缘	无
锁定插接部位	是
材料 - 金属	Copper Alloy
材料 - 接合部位电镀	Tin
材料 - 终端电镀	Tin
净重	0.950/g
方向	Straight
包装形式	Reel

调整片厚度	0.81mm
调整片宽	6.35mm
运行温度范围	-40° to +149° C
导线绝缘直径	4.05-4.90mm
线径规格 (AWG)	10, 12

可连接使用部件

描述	产品编号
Loxon Locking Quick Disconnect Housing, Nylon, UL94V-2, Natural	/content/molex/molex-dot-com/cn/zh/products/product-page.html/194390007.html
Loxon Locking Quick Disconnect Housing, Nylon, UL94V-0, Natural	/content/molex/molex-dot-com/cn/zh/products/product-page.html/194390008.html

施工工具

全局

描述	产品编号
Hand Crimp Tool for Locking Quick Disconnect Crimp Terminals, 10-12 AWG	2133094300
FineAdjust Applicator for Loxon Terminals, 10-12 AWG, UL 1015 Wire	2037029400