
产品编号 : 2145260601

Product Description : Micro-Lock Plus TPA Type Receptacle Housing, 1.25mm Pitch, Low-Halogen, Single Row, Positive Lock, 6 Circuits, Black

系列号 : 214526

状态 : Active

Product Category : Connector Housings



文件和资源

图纸

图纸 2145260601_sd.pdf

规格

应用规格 5055650000-AS-000.pdf

包装规格 2145269200-SPK-200.pdf

产品规格 2145260000-PS-000.pdf

产品规格 2145260001-PS-000.pdf

产品规格 2145260002-PS-000.pdf

产品规格 2145260003-PS-000.pdf

产物环境合规

合规

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

多部分产品合规性声明

- Eu RoHS
- REACH SVHC
- Low-Halogen

多部分行业合规性文件

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

欧盟 RoHS 合格证书

产品详情

常规

状态	活动
类别	Connector Housings
系列	214526
说明	Micro-Lock Plus TPA Type Receptacle Housing, 1.25mm Pitch, Low-Halogen, Single Row, Positive Lock, 6 Circuits, Black
应用	Wire-to-Board, Wire-to-Wire
产品系列	Micro-Lock Connector System
产品名称	Micro-Lock Plus
UPC	193264679874

机构

UL	E29179

物理

电路数（最多）	6
颜色-树脂	黑色
性别	Receptacle
符合灼热丝规范	否
插接极性	无
锁定插接部位	是
材料 - 树脂	PBT
净重	153.950/mg
行数	1
包装形式	Bag
面板安装式	否
间距 - 插配接口	1.25mm

间距 - 终端界面	1.25mm
有极性的插配件	是
运行温度范围	-40° to +105° C

可配插/可连接使用的产品

可配插部件

描述	产品编号
1.25mm Pitch Micro-Lock Plus Vertical, Single Row, Surface Mount Headers	505568
1.25mm Pitch Micro-Lock Plus Right-Angle, Single Row, Surface Mount Headers	505567
1.25mm Picth Micro-Lock Plus Vertical, Single Row, Surface Mount Headers with Potting Capability	205957
1.25mm Pitch, Micro-Lock Plus Single Row Plug Housings	214525
Micro-Lock Plus Vertical, Single Row, Through Hole Headers	220097
Micro-Lock Plus Right-Angle, Single Row, Through Hole Headers	220098

可连接使用部件

描述	产品编号
1.25mm Pitch Micro-Lock Plus TPA Retainers	214528
Micro-Lock Plus Female Crimp Terminals	214529