



P. C. B LAYOUT

材料Material
 原料Insulator:PBT(UL 94V-0)
 相关材料Related Material: Brass
 表面涂层Surface Coating: Au Over Ni

规格Specification
 额定电流Current rating:2.5AMP
 耐压Dielectric Withstanding Voltage:1000v Ac Min
 绝缘电阻Insulation Resistance:1000MΩ min
 接触电阻Contact resistance:20MΩ Max
 工作温度Working Temperature:-40℃~+105℃
 Max.Processing Temp瞬时温度:
 PBT 230° ±5° 10S

上海洲日电子有限公司

Shanghai Zhouri Electronics CO.,LTD

上海康司玛电子科技有限公司

Shanghai Consma Electronic Technology Co., Ltd

tel:021-51571121
 fax:021-51571120

http://www.zhouri.net
 http://www.ksmchina.com

产品名称:

PM 2.54-1*N

绘图:	牛万龙	日期:20250626
审核:	张海娜	日期:20250626
版本编号:	ZRLCGY2025-06-26-CJ A/2	

第三视角:

单位: mm

比例:

图幅:A4

页次 共 01 第 01