





NOTE:

1. MATERIAL:

a. HOUSING: PBT GLASS FIBRE UL94 V-0

b. CONTACT: BRASS T=0.25mm

(SURFACE PLATING: Au1u" + Sn80-100u" + Ni60u")

c. SHEET: BRASS T=0.3mm IRON T=0.3mm

(SURFACE PLATING: Cu80-100u" Ni80u"-100u")


2. ELECTRIC:

a. CONTACT RESISTANCE: 30 MILLIOHMS MAX

b. INSULATION RESISTANCE: 1000 MEGA OHMS MIN

c. DIELECTRIC VOLTAGE: 500V AC ONE MIN LEVEL

d. OPERATING TEMPERATURE: -55° -85°



P. C. B. LAYOUT

L&X 深圳市连欣科技有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X' ±0.5"	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: USB BF 90° DIP	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	XUBF-0214-0105
 UNIT: mm [inch] SCALE: 1:1 SIZE: A4	APPROVED BY: 邱国夷	DATE : 2014-02-23	MOLD NO.	
			DRAW NO:	HYC-USB14020105
			SHEET NO.	1 OF 1