HUBER+SUHNER® DATA SHEET
Within Series Adapter: 32_SMPX-50-0-1/111_N

Rev.: B



Description

Adaptor plug/plug
SMPX plug (male) / SMPX plug (male)

Interface standards
MIL-STD-348A/326_DESC 94007/94008

Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	40 GHz

Mechanical Data

Weight	0.0002 kg

Environmental Data

Operating Temperature	°C to °C
2002/95/EC (RoHS)	compliant

Material Data

Piece Parts (SMPX)	**Material**	**Surface Plating**
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	

Piece Parts (SMPX)	**Material**	**Surface Plating**
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	

Related Documents

Outline drawing	DOU-00013844

Ordering Information

Single package	32_SMPX-50-0-1/111_NE

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

WAIVER!
It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.

HUBER+SUHNER – Excellence in Connectivity Solutions

HUBER+SUHNER
HUBER+SUHNER AG
RF Technology
9100 Herisau, Switzerland
Phone +41 (0)71 353 41 11
Fax +41 (0)71 353 45 90
www.hubersuhner.com