

NOTES

MATERIAL

- 1.HOUSING MATERIAL: GLASS FILLED POLYESTER UL94V-0.
 - 2.CONTACT MATERIAL: PHOSPHOR BRONZE $\phi 0.46\text{mm}$.
 - 3.PLATING: GOLD FLASH PLATING OVER NICKEL.
 - 4.SHIELD: BRASS T0.20mm 40u" NICKEL PLATED.
- ELECTRICAL
- 1.VOLTAGE RATING: 125 VAC RMS.
 - 2.CURRENT RATING: 1.5 AMP.
 - 3.CONTACT RESISTANCE: 40 MILLIOHMS MAX.
 - 4.INSULATION RESISTANCE: 500 MEGOHMS MIN @ 100V DC .
 - 5.DIELECTRIC DIELECTRIC RESISTANCE: 500V DC RMS 50Hz. 1MIN.





MECHANICAL

- 1.DURRABILITY: 750 CYCLES MIN.
- 2.MATING/UNMATING FORCE: 2.24 KG.F MAX.


ENVIRONMENTAL:

- 1.STORAGE: $-40^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
- 2.OPERATION: $-40^{\circ}\text{C}\sim+85^{\circ}\text{C}$.

焊脚尺寸以顺畅过孔规为准



8	—
7	—
6	RX—
5	—
4	—
3	RX+
2	TX—
1	TX+
PIN	说明



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.35	X.*±3	APR.	Alex	TITLE: RJ45 56B 数据信号 DIP	
.XX±0.25	.X.*±2	CHK.	Jack	DWG NO. XY-RJ45R0-8PA-206	
.XXX±0.15	.XX.*±1*	DRA.	Can	CUSTOMER DRAWING	
SIZE A4	SCALE 1:1	SHEET 1/1	REV. A		