

Power cord (C13), VDE approved, 3 m

PC-186-VDE-3M



Features

- VDE approved power cord
- German Schuko input and C13 output
- Molded plugs with integrated strain relief

Specifications

Total length: 3 m

Input plug: Shuko type with ground contact hole and 4.9 mm pins

Output plug: C13

Wires: profile area 1 sq.mm, 10 A rated

Packaging

Q'ty in crtn, pcs
Crtn volume, CUM
Crtn weight, kgs
Individual package size LxWxH:
Carton size LxWxH:
Country of origin
Barcode
Customs code

40
0.045
14
245x135x40 mm
400x310x360 mm
CN
8716309037853
8544429090

Certificates

