This document was generated on 05/09/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 2153411214

Status: Active

Overview: Off-the-Shelf Pre-Crimped Leads

Description: Pre-Crimped Lead Mini-Fit Jr. Female-to-Pigtail, Gold (Au) Plating, 300.00mm Length, 18 AWG, Black



Series image - Reference only

Documents:

Drawing (PDF)
Datasheet (PDF)
RoHS Certificate of Compliance (PDF)

General

Product Family	Cable Assemblies
Series	215341
Application	Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Mini-Fit Jr. Term-to-Pigtail
Overview	Off-the-Shelf Pre-Crimped Leads
Product Name	Mini-Fit Jr.
Taxonomy	Power and Signal Cable Assembl
UPC	193264559527

Physical

Cable Length	300.00mm
Circuits (Loaded)	1
Color - Resin	Black
Gender	Female-Pigtail
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	5.064/g
Packaging Type	Bag
Single Ended	Yes
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.80-3.10mm
Wire Size AWG	18
Wire/Cable Type	UL 1015

Electrical

Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

Material Info

Reference - Drawing Numbers

Sales Drawing	2153411211-000

EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant

REACH SVHC
Not Contained per - D(2022)9120-DC (17 Jan 2023)

Halogen-Free Status
Not Low-Halogen

For more information, please visit Contact US

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
215341 Series

Use With
Mini-Fit Jr. Receptacle Housing 5557
Mini-Fit BMI Slide and Lock Panel Mount 44516
Mini-Fit BMI Panel Mount Receptacle Housing
 42474 , 43760

This document was generated on 05/09/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION