





| P/N                 | PIN   | DIM. A       | DIM. B     |
|---------------------|-------|--------------|------------|
| HMT-PM254-1*01Z-H85 | 1     | 0.00         | 2.54       |
| HMT-PM254-1*02Z-H85 | 2     | 2.54         | 5.08       |
| HMT-PM254-1*03Z-H85 | 3     | 5.08         | 7.62       |
| HMT-PM254-1*04Z-H85 | 4     | 7.62         | 10.16      |
| HMT-PM254-1*05Z-H85 | 5     | 10.16        | 12.70      |
| HMT-PM254-1*06Z-H85 | 6     | 12.70        | 15.24      |
| HMT-PM254-1*07Z-H85 | 7     | 15.24        | 17.78      |
| HMT-PM254-1*08Z-H85 | 8     | 17.78        | 20.32      |
| HMT-PM254-1*09Z-H85 | 9     | 20.32        | 22.86      |
| .....               | ..... | .....        | .....      |
| HMT-PM254-1*40Z-H85 | 40    | (PIN-1)X2.54 | (PIN)X2.54 |

|                                        |           |                                                                                                                                                                                   |                                                                                       |       |
|----------------------------------------|-----------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|-------|
| GENERAL TOLERANCES<br>UNLESS SPECIFIED |           | <div> 深圳市华明通电子有限公司</div> <div><b>HMTCONN</b> Shenzhen Huamingtong Electronics Co., Ltd</div> |                                                                                       |       |
| X.±0.30                                | X.°±5°    | PART NO.                                                                                                                                                                          | TITLE: 2.54FH H8.5 1xnPin                                                             |       |
| .X±0.20                                | .X°±1°    | HMT-PM254-1*NZ-H85                                                                                                                                                                | 180度 Y型 PC3.2 6T                                                                      |       |
| .XX±0.10                               | .XX°±0.5° | DESIGN: James                                                                                                                                                                     | CUSTOMER                                                                              | SIZE  |
| MANUFACTURE DWG                        |           | CHED: Talen                                                                                                                                                                       |                                                                                       | UNITS |
|                                        |           | APPD: Sophia                                                                                                                                                                      |  | SCALE |
|                                        |           |                                                                                                                                                                                   |                                                                                       | MM    |
|                                        |           |                                                                                                                                                                                   |                                                                                       | SHEET |
|                                        |           |                                                                                                                                                                                   |                                                                                       | N:A   |
|                                        |           |                                                                                                                                                                                   |                                                                                       | 1/1   |