东莞市讯普电子科技有限

Dongguan Xunpu Electronic Technology Co.,

承　认　书

SPECIFICATION FOR APPROVAL

客 户 名 称 Customer：_____

贵司料号CUSTOMER P/N：_____

FFC cable 1.0mm,30P,total length 100mm,reverse,gold finger 4mm,reinforcing plate 8mm


敝司料号INTERIOR P/N：FFC-1.0-30-100-B-4-8


贵公司承认印 Approal slgnatures


料 号/Part No.	签　章/Signatures

Send us a copy of reference, thank you!　　日期 Date:

拟制/Drawn	李晓
审核/Check	陈军
批准/Approved	钰







Structure				
NO.	Project	Specification		Remark
1	Insulating film	Print 20624	43um	60V 80C
		Blank film	43um	
2	Stiffeners	Blue	225um	PET
3	Conductor tinning	Thickness	0.035	±0.005
		Width	0.3	±0.03
4	Conductor plating	Electroplate	Tin Sn	⩾40u"
		Electroplate		

Size			
Number of conductor cores	N	30	
Spacing	P	1.0	±0.05
Total spacing	Pt	29	±0.08
Overall width	W	31	±0.08
Edge width	M	1.0	±0.08
Overall length	L	100	±1.5
Mating thickness	T1	0.3	±0.05
Thickness of the thread	T2	0.12	±0.03
The inclination of the line mouth	A		⩽0.3
Punching inclination	B		⩽0.5
The length of the bare copper at the wire port	S1/S2	4/4	±0.05
Length of stiffener	B1/B2	8/8	±1

Ancillary checklists			
NO.	Project	Specification	Quantity
1			
2			
3			

Precautions

1. The body image is for relationship comparison only, and everything is subject to the specifications of the data sheet.

1. Shelf life: 12 months for gold plating; Tin plating for 6 months.
2. Storage environment: temperature 0°C'38°C; Humidity 20%'70%RH.

Specifications and models:	FFC-1.0-30-100-B-4-8		
Customer part number:		Customer model:	

XunPu 东莞市讯普电子科技有限公司

Version	Content of change	date	Name:	FFC flexible cable	Figure number:	XP2024080501	Drawing:	Li ming
A/O	New production	2022/09/05	Proportion:	FIT	Unit:	Millimetre(mm)	Audit:	Chen Jun
			Vision:		Page number:	Page 1 of 1	Approved:	Xiang Yu