



MATAL	X
SUS	0.2mm
PBS	0.25mm

PIN	φ1.65	φ2.0	φ2.5
APPD.		✓	



SCHEMATIC

NO.	PART NAME	MATERIAL	QTY	FINISHING	TOLERANCE UNLESS SPECIFIED		NO	DATE	REVISIONS	BY	APPD
					UP TO 5mm: ±0.1	ANGULAR ±1°					
6	DC-005 PING	BRASS	1	Ni PLATED	UP TO 5mm: ±0.1	ANGULAR ±1°	1				
5	DC-005CA 4#FLAT PIECE	BRASS	1	Ag PLATED	ABOVE 5mm: ±0.2	±1°					
4	DC-005 2#CURVE PIECE	BRASS	1	Ag PLATED	TITLE:DC JACK						
3	DC-005 3#SPRING	SUS/PBS	1	Ag PLATED	MODEL: DC-005J-2.0-PU						
2	DC-005 COVER	PBT	1	BLACK/WHITE	UNIT : MM	SCALE: 4:1					
1	DC-005 CASE	PBT/PA6T+PA66	1	BLACK/WHITE	HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司						
									ROHS COMPLIANT	DWN	
									CHK'D		
									APPD		
									PRO.AGL:		REV : A