





**SPECIFICATION**

Contact Rating: 50mA, 12V DC  
 Contact Resistance: 100MΩ max  
 Insulation Resistance: 100MΩ min. 500V DC  
 Dielectric Strength: 250V AC/1minute  
 Travel: 0.20mm  
 Operating Temp: -25°C~+70°C  
 Storage Temp: -25°C~+70°C



PAPT NO	TS-3025-X-X-X
Operating Force	A:160gf B:260gf C:350gf
Height	H:A:1.5 B:1.6 C:1.7
Fixed column	A:With B:without



ITEM	PAPT NAMF	TER,NO	QTY	MATERIAL	FINISHING	REMARK
⑤	Terminal	—	2	Brass (0.30t)	Plating silvering	——
④	Contact	—	1	F.ag/Sus	Natural	——
③	Base	—	1	LCP		——
②	Cover	—	1	Spcc	Plating Nickel	——
①	Keystake	—	1	Pa46		——

广东星坤科技股份有限公司

日期

文件工程章

REVISIONS	DATE	REVISED	APPROVED	DESCRIPTION

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5

UNSPECIFIED TOLERANCES

**XKIB**

DSND	SCALE: N/A	MODEL TYPE: <b>TACT SWITCH</b>
DWN	VIEW:	PART NO.: <b>TS-3025-X-X-X</b>
CHKD	UNIT: mm/in	DWG NO.:
APPD	SIZE: A4	

**XKB INDUSTRIAL PRECISION CO., LIMITED**

WEIGHT	SHEET	REVISIC
	1/1	A0