



NO.1			
PART NO	F	H	
XX	2.5	3.8	
XX	2.5	4.3	
XX	2.5	4.8	
XX	2.5	5.0	
XX	2.5	5.5	
XX	2.4	6.0	
XX	2.4	6.5	
XX	2.3	7.0	
XX	2.3	7.5	
XX	2.3	8.0	
XX	2.3	8.5	
XX	2.3	9.0	

NO.2	
PART NO	vigor
70	70±30
100	100±50
160	160±50
250	250±50
320	320±80
350	350±80
520	520±130

ITEM	PART NAME	QTY.	MATERIAL	FINISHING
⑤	Terminal	4	Brass(0.30t)	Plating silver
④	Contact	1	F.Ag/SUS	
③	Base	1	PA46	Black
②	Cover	1	SUS	
①	Keystoke	1	PA46	Black

APPROVALS		DATE	DRAWING NO.	
DRAWN	G.M Chen	2026/05/25	ELECTRONICS CO.,LTD	
CHECKED			TACT SWITCHS	
APPROVALS		PART NO.	TD-1150SR-XXH-XXX	
TOLERANCES ARE		SCALE: 1:1	PROJ. SHEET 1 OF 1	
30~0.1	±0.30	ANGLE		
10~0.30	±0.20	UNIT: mm		
5~0.10	±0.15	DRAWING NO.		
~5	±0.10			
ECN NO.	REV	DATE.	DESCRIPTION.	CHANGE.
	A		NEW	