THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION –,– .
© COPYRIGHT – By – ALL RIGHTS RESERVED.

LOC	DIST
AF	50


REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A2	ECR-13-016672	25OCT13	PKS	RRP


1 CONTINUOUS STRIP ON REELS WITH TERMINALS LOCATED ON .220±.003 CENTERS


2 SLOT TERMINATES A SINGLE MAGNET WIRE ONLY. ALUMINUM RANGE: 0.97–1.22mm [#18.5–#16.5] AWG.

3 AFTER INSERTION INTO PLASTIC HOLDER TAB PORTION MUST BE BENT OVER 45° TO 90° OR POTTED–IN TO PREVENT PULL–OUT WHEN MATING RECEPTACLE IS DISCONNECTED.









1742474

1742474–1

PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN jr ruth 12SEP06	TE Connectivity
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± – ; 1 PLC ± – ; 2 PLC ± – ; 3 PLC ± .010 ; 4 PLC ± – ; ANGLES ± 5'	CHK K RANDOLPH 12SEP06	NAME TERMINAL, TAB, .187 FASTON, MAG–MATE –
		APVD K RANDOLPH 12SEP06	
		PRODUCT SPEC —	
		APPLICATION SPEC —	SIZE A2 · CAGE CODE 00779 · DRAWING NO C–1742474 · RESTRICTED TO —
MATERIAL BRASS	FINISH TIN PLATE	WEIGHT –	
		CUSTOMER DRAWING	SCALE 10:1 · SHEET 1 OF 1 · REV A2