Data sheet

2552.0 FSH 6/6,3



Crimp lug, Spade flat plug shape acc. to DIN 46245 part 1 - 3, Length: 23.8 mm, Max. wire cross-section: 6 mm², Colour: Yellow

RAL: 1026

Data sheet

2552.0 FSH 6/6,3

Business data

Article number	2552.0
Article name	FSH 6/6,3
GTIN (EAN)	4044211053451
Connector shape	Spade flat plug shape acc. to DIN 46245 part 1 - 3
Product-compliant (according to DIN)	yes
Packaging unit	100
Quantity unit	PC
Weight per piece (not including packaging)	1.66 g
Weight per piece (including packaging)	1.75 g
Unit of weight	G
Customs number	85369010
Country of origin	TW
Product description	Crimp
Colour	Yellow

Data sheet

2552.0 FSH 6/6,3

Technical data

Dimensions	
Length	23.8 mm
Length of connector	7.8 mm
Plug width	6.3 mm
Diameter of feed-in funnel	6.2 mm
Plug thickness	0.8 mm
Size DIN	6,3 - 6

Connection data	
Wire cross-section, min.	4 mm²
Wire cross-section, max.	6 mm²
Wire cross-section AWG, min.	12
Wire cross-section AWG, max.	10

Materials	
Connector material	Copper
Surface	Tin-plated
insul.	Expanded PVC insulation
Working temperature, min.	-10 °C
Working temperature, max.	75 °C

Further technical data	
Insulation available	✓

Environmental Product Compliance	
REACH Conform	yes
REACH Reference date	2023-06-14
REACH Candidate Substance Note	No
RoHS Conform	yes

Data sheet
2552.0 FSH 6/6,3

Media

Accessories