ATGBICS

ATGBICS DAC-Q56DD-400G-2.5M Dell Compatible Direct Attach Copper Twinax Cable 400G QSFP-DD (2.5m, Passive)



Brand : ATGBICS

Product code: DAC-Q56DD-400G-2.5M-C

Product name : DAC-Q56DD-400G-2.5M Dell Compatible Direct Attach Copper Twinax Cable 400G QSFP-DD (2.5m, Passive)

DAC-Q56DD-400G-2.5M Dell Compatible Direct Attach Copper Twinax Cable 400G QSFP-DD (2.5m, Passive)



ATGBICS DAC-Q56DD-400G-2.5M Dell Compatible Direct Attach Copper Twinax Cable 400G QSFP-DD (2.5m, Passive):

ATGBICS DAC-Q56DD-400G-2.5M compatible 400GBase-CU QSFP-DD to QSFP-DD direct attach cable operates over passive copper with a cable length of 2.5m. It is suitable for short reach connection between two QSFP-DD ports in 400G interconnecting networking applications. Our product meets the specification of Dell DAC-Q56DD-400G-2.5M= and we proudly offer a compatibility guarantee and lifetime warranty. Our rigorously tested products record a unique traceable serial number and are fully compliant with all MSA Standards and protocols including QSFP-DD MSA.
ATGBICS DAC-Q56DD-400G-2.5M Dell Compatible Direct Attach Copper Twinax Cable 400G QSFP-DD (2.5m, Passive). Cable length: 2.5 m, Connector 1: QSFP-DD, Connector 2: QSFP-DD, Data transfer rate: 400000 Mbit/s

Features	
Product colour *	Black
Cable length *	2.5 m
Connector 1 *	QSFP-DD
Connector 2 *	QSFP-DD
Connector 1 gender *	Male
Connector 2 gender *	Male
Jacket material	Polyvinyl chloride (PVC)
Conductor material	Copper
Ethernet interface type	400 Gigabit Ethernet
AWG wire size	28
Data transfer rate	400000 Mbit/s

Features	
Plug and Play	✓
Certification	CE, FCC, RoHS
Country of origin	United Kingdom
Operational conditions	
Operating temperature (T-T)	0 - 70 °C
Storage temperature (T-T)	-40 - 80 °C
Operating relative humidity (H-H)	10 - 90%
Storage relative humidity (H-H)	10 - 85%
Packaging data	
Quantity per pack	1 pc(s)



5056468760098

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 21-SEP-2023. Prints or copies of Information are only valid on the printed Publication date