


1	5	6	7	8	
Dept	REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
Qty	A	NEW RELEASE	WPY 09/13/25'		
DC					
ED					
IE					
ISO					
PD					
R&D					
SD					
QA					
QC					
QF					

晨翔2.54mm 短路帽 H=6.0 开口 黑色胶芯 半金镍端子

晨翔料号:DS1027-2AB20

The information provided herein is from CONNELY Electronic Co., Ltd. and is confidential. Any disclosure to a party other than the recipient is prohibited. The intellectual properties and its rights contained herein, including but not limited to, trademarks, patents, copyrights, trade secrets, and technical know-how, are owned exclusively by CONNELY or its affiliates. Unauthorized use of this information in any format or manner. CONNELY may enforce its intellectual property rights at its own discretion; failures or delays to exercise such rights does not constitute a waiver of such rights.

- 备注:
- 电性说明:
 - 接触阻抗: 30毫欧最大
 - 额定电流: 3安
 - 环境特性:
 - 工作温度: -40~+105° C
 - 材料:
 - 端子: H62铜, 镀半金镍
 - 胶芯: PBT, 黑色, 阻燃



GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION		TITLE	2.54mm Mini Jumper		
X.	±0.60	X.	±5°	UNITS	mm	SHEET SIZE	A4	SERIES	DS1027 SERIES
.X	±0.38	.X	±3°	晨翔电子有限公司 CONNELY CONNELY ELECTRONIC CO. LTD					
.XX	±0.25	.XX	±2°						
DRAWING TYPE		CUSTOMER							
SCALE		1:1	SHEET	1 OF 1					
DRAWING NO.		C-DS1027-XXXXX-A							