



东莞市讯普电子科技有限公司

Dongguan Xunpu Electronic Technology Co., Ltd

承 认 书

SPECIFICATION FOR APPROVAL

客户名称 Customer: _____

贵司料号CUSTOMER P/N: _____

FFC cable 0.5mm 30P, total length 100mm, co-directional, gold finger 4mm, reinforcing plate 8mm

敝司料号 INTERIOR P/N: FFC-0.5-30-100-A-4-8

贵公司承认印 Approval signatures


料号/Part No.	签章/Signatures

Send us a copy of reference, thank you!

日期 Date:

拟制/Drawn	李明
审核/Check	李军
批准/Approved	向钰





Structure				
NO	Project	Specification	Remark	
1	Insulating film	Print 20624	43um	60V 80C
		Blank film	43um	
2	Stiffeners	Blue	225um	PET
3	Conductor tinning	Thickness	0.035	± 0.005
		Width	0.3	± 0.03
4	Conductor plating	Electroplate	Tin Sn	$\geq 40\mu$
		Electroplate		

Size			
Number of conductor	N	30	
Spacing	P	0.5	± 0.05
Total spacing	Pt	14.5	± 0.08
Overall width	W	15.5	± 0.08
Edge width	M	0.5	± 0.08
Overall length	L	100	± 1.5
Mating thickness	T1	0.3	± 0.05
Thickness of the	T2	0.12	± 0.03
The inclination of the	A	—	≤ 0.3
Punching inclination	B	—	≤ 0.5
The length of the bare	S1/S2	4/4	± 0.05
Length of stiffener	B1/B2	8/8	± 1.5


Ancillary checklists			
NO	Project	Specification	Quantity
1			
2			
3			


Precautions

1. The body image is for relationship comparison only, and everything is subject to the specifications of the data sheet.

1. Shelf life: 12 months for gold plating; Tin plating for 6
2. Storage environment: temperature 0°C-38°C; Humidity

Specifications and models:	FFC-05-30-100-A-4-8		
Customer part number:	Customer model:	date	
Version	What's Changed	date	
A/O	New production	2022/09/05	

 **XunPu** 东莞市讯普电子科技有限公司

Name:	FFC flexible	Figure number:	XP2022090501	Drawing:	Li ming
Proportion:	1:1	Unit:	Millimetre(mm)	Audit:	Chen Jun
Vision:		Page number:	Page 1 of 1	Approved:	Xiang Yu