





PCB LAYOUT



Specifications :

Voltage rating:100V AC / DC
Current rating: 2A AC / DC
Withstanding voltage: 500V AC/minute
Temperature range: -40°C~+85°C
Insulation resistance: ≥500MΩ
Contact resistance: ≤20mΩ
After environmental testing : ≤40mΩ

X1515 W R S-03-LP SW
① ②③④ ⑤ ⑥ ⑦

① Series No.
② Category : W-WAFER
③ Welding Board Angle : R-Straight 90°
④ Welding Way:S-SMT
⑤ Row No.-Pin No.: XX-02P~15P
⑥ Material : LP-LCP 94V-0
⑦ Plating Category: SW-Matte Tin Plating

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	7.30	1.50	4.45	09	17.80	12.00	14.95
03	8.80	3.00	5.95	10	19.30	13.50	16.45
04	10.30	4.50	7.45	11	20.80	15.00	17.95
05	11.80	6.00	8.95	12	22.30	16.50	19.45
06	13.30	7.50	10.45	13	23.80	18.00	20.95
07	14.80	9.00	11.95	14	25.80	19.50	22.45
08	16.30	10.50	13.45	15	26.80	21.00	23.95

X1515WRS-03-LPSW	LCP UL 94V-0	Phosphor Bronze	X1515H
PART N0	Material	Material(Pin)	Suitable XKB Housing

					ANGLAR	±5°
ΔX					L≤ 4	±0.2
ΔX					4<L≤ 16	±0.3
ΔX					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: 1.5mm Crimp Style Connectors
DWN		VIEW:	PART NO.: X1515WRS-03-LPSW
CHKD		UNIT: mm/in	DWG NO.: X-X1515WRS-03-LPSW
APPD		SIZE: A4	

WEIGHT	SHEET	REVISION
	1/1	A0