





3D
VIEW



LB615-XXP-WOR

PACKING: R:REEL
RUNNING NUMBER
COLOR:WHITE
P: PLUG
PIN
PLATING: G:GOLD FLASH
X:10u"SELECTIVE GOLD IN CONTACT AREA,MATTE TIN ON TALL
Y:ALL GOLD PLATING 10 u"
HIGHLY
6:0.5 BTB
LXWCONN BTB CONNECTOR SERIES

Electrical

Voltage:50 V AC(rms)/DC
Current:0.5A AC(rms)/DC
Contact Resistance:60 mΩmax(initial)
Dielectric Withstanding Voltage:200 V AC/rms
Insulation Resistance:500 MΩ min
Operating Temp:-25℃+85℃

MATERIAL:

HOUSING:LCP NATURE(UL94V-0)
TERMINAL:PHOSPHOR BRONZE C5191R-H

P 数	尺寸			P 数	尺寸		
	A	B	C		A	B	C
8	5.00	2.90	1.50	48	15.00	12.90	11.50
10	5.50	3.40	2.00	50	15.50	13.40	12.00
12	6.00	3.90	2.50	52	16.00	13.90	12.50
14	6.50	4.40	3.00	54	16.50	14.40	13.00
16	7.00	4.90	3.50	56	17.00	14.90	13.50
18	7.50	5.40	4.00	58	17.50	15.40	14.00
20	8.00	5.90	4.50	60	18.00	15.90	14.50
22	8.50	6.40	5.00	62	18.50	16.40	15.00
24	9.00	6.90	5.50	64	19.00	16.90	15.50
26	9.50	7.40	6.00	66	19.50	17.40	16.00
28	10.00	7.90	6.50	68	20.00	17.90	16.50
30	10.50	8.40	7.00	70	20.50	18.40	17.00
32	11.00	8.90	7.50	72	21.00	18.90	17.50
34	11.50	9.40	8.00	74	21.50	19.40	18.00
36	12.00	9.90	8.50	76	22.00	19.90	18.50
38	12.50	10.40	9.00	78	22.50	20.40	19.00
40	13.00	10.90	9.50	80	23.00	20.90	19.50
42	13.50	11.40	10.00				
44	14.00	11.90	10.50				
46	14.50	12.40	11.00				

LXW 连兴旺电子(深圳)有限公司
connectivity LXWCONN ELECTRONICS (SHENZHEN) CO., LTD

制图 (DR):	Kavin 2020.08.31	品名(TITLE):	0.5mm 单槽公座无柱
审核 (CHKD):		料号(PART NO):	LB615-XXP-WOR
核准 (APPD):	Tong 2020.08.31	比例(SCALE):	1:8
		单位(UNITS):	mm
		张数(SHEET):	1 OF 1
		图幅(SIZE):	A4

RECOMMENDED PCB PATTERN DIM.
TOLERANCE : ±0.05



修订 SER	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE

一般公差 GENERAL TOLERANCE	
.X	±0.15
.XX	±0.10
.XXX	±0.05
ANGLES	±2°

