








△2 TABLE 1

SUB ASSEMBLY PART NO. AND CH. CODE	NO.	PART NO. AND CH. CODE	MATERIAL	COLOR	QTY.
7282-1100 ETC.	①	SEE TABLE 2	△3 HPA	SEE TABLE 2	1
	②	7157-4024	△3 HPA	NATURAL	1

△4 TABLE 2

	SUB ASSEMBLY PART NO. AND CH. CODE	PART NO. AND CH. CODE	COLOR
	7282-1100, A	7182-1100	NATURAL
	7282-1100-10, A	7182-1100-10	DARK GRAY
	7282-1100-30, A	7182-1100-30	BLACK
	7282-1100-40, A	7182-1100-40	LIGHT GRAY
	7282-1100-50, A	7182-1100-50	ORANGE
△1	7282-1100-60, A	7182-1100-60	GREEN
△5	7282-1100-80, A	7182-1100-80	BROWN
	7282-1100-90, A	7182-1100-90	BLUE

NOTES

1. MATING PART NO. : 7283-1100 ETC.
2. APPLICABLE TERMINAL NO. : 7114-4020 ETC.

注 記

1. 嵌合相手品番 : 7283-1100 ETC.
2. 適用端子品番 : 7114-4020 ETC.

LET	DATE	REVISION RECORD	NO.	CHKD
△5	04.05.18	ADDED COLOR PART NO.	C04-Z497	Y. I
△4	98.12.23	ELIMINATED COLOR NO.	C98-N179	T. M
△3	95.03.20	CHANGED MATERIAL, A	C95-L362	M. K
△2	93.10.30	CHANGED MATERIAL & ADDED COLOR NO.	C93-P172	C. M
△1	90.05.11	CHANGED FORM & ADD PART NO.	C90-L468	H. Y
	88.12.24	NEW	C89-L010	K. J

GENERAL TOLERANCE						
	10MAX	50MAX	100MAX	250MAX	2500VR	ANGLE	ECCENT
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30′	0.1
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30′	0.1
C	±0.3	±0.5	±0.8	±1.4	±2	±30′	0.15

SPECIFIED

MASS g

CUSTOMER

CUSTOMER PART NO.	CUSTOMER DWG NO.
OFFICE	TRIAL PART NO.
VENDOR	
VENDOR NO.	

DWG TYPE	DWG SOURCE	DWG DATE	UNIT	SCL	ANGLE
R	NEW	89.01.11	mm	2/1	3

APPROVED	CHECKED	CHECKED	DESIGN	DRAWN
H. ISHIDA	T. HIRAKAWA	Y. IKEDA	Y. OHTA	J. GODINEZ
'04.5.18	'04.5.18	04.05.18	88.04.15	04.05.18

ISSUE MARK

MATL. SPEC. SEE TABLE 1

TREAT. & FIN.

NAME △5 2.3II (090II) 10P CONNECTOR

SUB ASSEMBLY MALE

PART NO. CH. CODE 7282-1100 ETC.

DWG NO. 7282-1100:R

SET DWG NO.

YAZAKI CORPORATION