

THIS IS ISSUED IN STRICT CONFIDENCE THAT IT IS NOT USED AS A BASIS FOR MANUFACTURE OR SALE AND THAT IT IS NOT COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE PRIOR WRITTEN CONSENT OF CAL TEST ELECTRONICS, INC.

- 4mm BANANA PLUG LEAD, SHEATHED PLUG TO SHEATHED PLUG, 0.75mm², SILICONE JACKETED WIRE.
CE MARK AND CSA LISTED (US AND CANADA).
- SPECIFICATIONS:
WIRE:
REINFORCED SILICONE (-60° C TO +180° C)
195x0.07mm STRANDED BARE COPPER, 0.75mm² CROSS SECTION, 18 AWG, Ø.146±.008 (Ø3.7±0.2mm) O.D.

INSULATED HOUSING:
POLYPROPYLENE THERMOPLASTIC, UL94V-0.

CONTACT:
4mm, 9 LEAF, BERYLLIUM COPPER, NICKEL PLATED.
PLUG BODY:
BRASS, NICKEL PLATED.
- RATING:
IEC 61010-031 @ 1,000 V CAT IV P2.
CURRENT: 12 A MAX.
INTERNAL RESISTANCE: 55 mΩ MAX @ 200 cm LENGTH.
TEMPERATURE: -25° C TO +80° C.



CE DECLARATION OF CONFORMITY, LVD
CONFORMS TO RoHS DIRECTIVE 2002/95/EC.

REVISIONS			
REV.	DESCRIPTIONS	DATE	APPROVED
-	CLASS A RELEASED	7/12/99	
A	NOTE 3: ADDED IEC 61010-031 1,000 V CAT IV & RoHS; REVISED PLUG CONFIGURATION, PAGE 2.	2/7/05	

PART NUMBER


CT2162-L-#

COLOR: 0 - BLACK
2 - RED
4 - YELLOW
5 - GREEN
6 - BLUE
9 - WHITE

LENGTH: (CENTIMETERS)
STANDARDS: 10, 25, 50, 100, 150, 200

THIRD ANGLE PROJECTION		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ± 1/32 .XX ± .02 .XXX ± .005 DO NOT SCALE DRAWING		CONTRACT NO.		Cal Test Electronics 22820 Savi Ranch Parkway Yorba Linda, CA 92887-4610			
		MATERIAL		APPROVALS		DATE		LEAD, 4mm SHEATHED PLUGS, 0.75mm², SILICONE	
		FINISH		DRAWN WDH		7/12/99			
NEXT ASSY		USED ON		ENGR.		SIZE A		CAGE CODE 43F45	
APPLICATION				DESIGN ACTIVITY		DWG. NO. P217600		REV. A	
						SCALE NONE		SHEET 1 OF 2	

THIS IS ISSUED IN STRICT CONFIDENCE THAT
IT IS NOT USED AS A BASIS FOR
MANUFACTURE OR SALE AND THAT IT IS NOT
COPIED, REPRINTED OR DISCLOSED TO A
THIRD PARTY EITHER WHOLLY OR IN PART
WITHOUT THE PRIOR WRITTEN CONSENT OF
CAL TEST ELECTRONICS, INC.



DRAWN		WDH	7/12/99	SIZE	A	CAGE CODE	43F45	DWG. NO.	P216200	REV.	A
CHECKED				SCALE	1:1				SHEET	2	