# Data Sheet

HUBER+SUHNER

## Coaxial Cable Connector
## 16_SMA-50-4-165/199_N

## Description

Right angle cable plug

Interface standards
SUHNER-SMA-26.5GHz



## Technical Data

### Electrical Data

| | | |
|---|---|---|
| Impedance | 50 Ω | |
| Interface frequency max. | 11 GHz | |
| Frequency range | DC to 6 GHz | 6 to 11 GHz |
| Return loss | 25 dB | 15 dB |

### Mechanical Data

| | |
|---|---|
| Centre contact | plugged |
| Outer contact | clamped |
| Weight | 0.0145 kg |

### Environmental Data

| | |
|---|---|
| Operating temperature | -60 °C to 165 °C |
| 2011/65/EU (RoHS - including 2015/863 and 2017/2102) | compliant |

### Material Data

| Piece Parts | Material | Surface Plating |
|---|---|---|
| Centre contact | Copper Beryllium Alloy | Gold Plating (Nickel underplated) |
| Outer contact | Stainless Steel | |
| Body | Stainless Steel | |
| Insulator | PTFE (Polytetrafluoroethylene) | |
| Coupling nut | Stainless Steel | |
| Gasket | VMQ (Silicone rubber) | |

## Related Documents

| | |
|---|---|
| Outline drawing | DOU-00146342 |
| Catalogue drawing | DCA-00130018 |
| Assembly instruction | DOC-0000294172 |

## Ordering Information

| | |
|---|---|
| Single package | 16_SMA-50-4-165/199_NE |

## Additional Information

| | |
|---|---|
| Suitable cables | EACON_4C |



Waiver: It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general information purposes only.