PINTECH 品致®

OSCILLOSCOPE PROBE CP-3601R



Characteristic

- The oscilloscope probe CP series is the most widely used oscilloscope probe. At the same time, it is the most durable and economical probe. There are no active components such as transistors or amplifiers in passive probes, so there is no need to power the probe.

Model	CP-3601R
Feature	Precision
Attenuation Ratio	10X
Accuracy	±0.5%
Bandwidth	DC-600MHz
Rise time	0.58ns
Input impedance	10MΩ
Input capacitance	12pF
Working voltage	600V
Working Temperature	0~50°C
Cable length	1.2m
Weight	150g

● ACCESSORIES



Insulated Tip | Measuring Tip | Spring Hook | Adjustment Tool | Integrated Circuit Frontier | The Probe Tip Is Grounded | PL-15 | Channel Identifier

GUANGZHOU PINTECH CO.,LIMITED
Web:www.pintech.com.cn
Tel:86-20-82510899
E-mail:sales@pintech.com.cn

Main Products

Optical Isolated Voltage Probe, Differential probe, Oscilloscope probe, High voltage probe, High frequency current probe, Current probe, Digital high voltage meter, High voltage amplifier, Power amplifier, ESD generator, Function generator, Oscilloscope, Spectrum analyzer, multimeter, High voltage power supply, AC power supply, DC power supply and Power equipment instrument.