






CIRCUIT DIAGRAM



The Main Thchnology Performance

Rate voltage,current	50mA DC12V
Contact resistance	≤100mΩ
Operating force	±30gf
Travel	0.20±0.10mm
Insulated resistance	≥100MΩ
Dielectric strength	≥250VAC/1min



PCB.WELDING DRAWING

E	按钮	PPA	1	黑色
D	盖板	铁盖板	1	镀铜锡
C	弹片	不锈钢	1	镀银
B	本体	PPA	1	黑色
A	卡件	黄铜	1	镀银
ITEM	DESCRIPTION	MATERIAL	QTY	FINSH/COLOR

T S O 9 - C B W 1

力度: F: 250G
E: 180G

高度: H4.3
H4.5
.....

H	H	H
3.5	5.5	8.0
3.8	6.0	8.5
4.3	6.5	9.0
4.5	7.0	9.5
5.0	7.5	10.0

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	Alex	TITLE: 4.5x4.5 DIP TACT SWITCH	
.X±0.35	X.*± 5°	CHK.	Jack	DWG NO. TS09-CBW1EHX	
.XX±0.25	.X*± 3°	PROJ.	Can	CUSTOMER DRAWING	
.XXX±0.15	.XX*± 1°	SIZE	A4	SCALE	1:1
		SHEET	1/1	REV.	A