This document was generated on 01/31/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 1301430151

Status: Active

Overview: Watertite Extreme Wet-Location Wiring Solutions

Description: Watertite Extreme Cordset 14 Gauge SJOW, 2 Pole/3 Wire, Cordset Length 30.48m (100.0'), NEMA 5-15, 125V, Inline GFCI



Series image - Reference only

Documents:

Drawing (PDF)
Brochure (PDF)
RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR6837
UL	E38085
General	
Product Family	Wiring Devices
Series	130143
IP Rating	IP67
NEMA Configuration	NEMA 5-15
Overview	Watertite Extreme Wet-Location Wiring Solutions
Product Name	Watertite Extreme
Receptacle Type	Single
Specialty	N/A
Taxonomy	Wiring Devices
Type	Cordset
UPC	78678899576
Physical	
Cord Grip Body Size	F2 1/2"
Flange	No
Flip Lid	No
Gender	Male-Female
Length	30.48m (100.0')
Locking Blade	No
Net Weight	999.000/kg
Poles	2-pole/3-wire
Electrical	
Cord Type	14/3 SJOW
Current - Maximum per Contact	15.0A
GFCI	Yes-In-line
Lighted Connector	No
Voltage - Maximum	125V
Material Info	
Engineering Number	14W47D143IN
Reference - Drawing Numbers	
Sales Drawing	1301430151-000

EU ELV
Not Reviewed

EU RoHS
Not Reviewed

China RoHS

REACH SVHC
Not Reviewed

Halogen-Free Status
Not Reviewed

For more information, please visit Contact US

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
130143 Series

This document was generated on 01/31/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION