



■ Specifications.

- Voltage rating: 250V AC/DC
- Current rating: 5A AC/DC
- Withstanding voltage: 1500V AC/minute
- Temperature range: -25 °C ~ +85 °C
- Insulation resistance: 1000mΩ Min
- Contact resistance: 20mΩ Max
- Material: Phosphor bronze Tin-plated
- Applicable Wire Sizes: AWG#18~22

X5080 T -P SN- H  
① ② ③ ④ ⑤

- ① Series No.
- ② Category : T-Trrminal
- ③ Material: P-Phosphor bronze
- ④ Plating style: SN-Bright Tin plating
- ⑤ H-High

X5080T-PSN-H	Phosphor bronze	AWG#18-22	TIN Plated	X5080H
PART NO	Material	Wire Range	Finish	Suitable XKB Housing

广东星坤科技股份有限公司

生效日期

文件工程章

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5



DSND	SCALE: N/A
DWN	VIEW:
CHKD	UNIT: mm/in
APPD	SIZE: A4

MODEL TYPE:	5.08mm Crimp Style Connectors
PART NO.:	X5080T-PSN-H
DWG NO.:	X-X5080T-PSN-H

XKB INDUSTRIAL PRECISION CO., LIMITED

WEIGHT	SHEET	REVISION
	1/1	A0