**Part Number :** 1301430396
**Product Description :** Super-Safeway Cordset, 6 Gauge SOOW, 3 Pole/4 Wire, Cordset Length 7.62m (25.0'), Non-NEMA California Style Locking Blade, 50.0A, 125V /250V
**Series Number :** 130143
**Status :** Active
**Product Category :** Wiring Devices
**Engineering Part Number :** CS6365NA064



## Documents and Resources

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | Not Reviewed per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21 |
| REACH SVHC | Not Reviewed per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Not Reviewed per EU 2015/863 |

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Wiring Devices |
| Series | 130143 |
| Description | Super-Safeway Cordset, 6 Gauge SOOW, 3 Pole/4 Wire, Cordset Length 7.62m (25.0'), Non-NEMA California Style Locking Blade, 50.0A, 125V /250V |
| IP Rating | N/A |
| NEMA Configuration | Non-NEMA Locking CA |
| Product Name | Super-Safeway |
| Specialty | N/A |
| Type | Cordset |
| UPC | 78172557131 |

### Electrical

| | |
|---|---|
| Current - Maximum per Contact | 50.0A |
| GFCI | No |
| Voltage - Maximum | 125V / 250V |

### Physical

| | |
|---|---|
| Cord Type | 6/4 SOOW |
| Flange | No |
| Flip Lid | No |
| Gender | Male-Female |
| Length | 7.62m (25.0') |
| Lighted Connector | No |
| Locking Blade | Yes |
| Poles | 3-pole/4-wire |
| Receptacle Type | Single |
| Wire Size (AWG) | 6 |