




A4				 台普 ROCPCU	COMMON TOLERANCE X.XX ± 0.10 X.X ± 0.15 X ± 0.25 ANGULAR —	UNIT	MM	PROJECTED		PRODUCT NAME:	
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91951P6GS
A2							DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1							ROCPCU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION			ISSUE	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission				

	A	B	C	D	E	F	G		
1	<p>性能参数</p> <ol style="list-style-type: none"> Nut assembly torque:5-14N 螺帽装配力矩:5-14N Protection level:IP67 防护等级:IP67 Explosion prevention level: IK10 防暴等级: IK10 Working environment temperature: -20 °C~+55 °C 工作环境温度: -20 °C~+55 °C LED voltage: 6V LED 电压: 6V LED lamp power consumption: 20m以下 LED灯功耗: 20m以下 LED lamp lifespan: 40000h LED寿命: 40000h LED color: Greed LED颜色: 绿色 								
2									
3									
4	<p>连接形式</p> <ol style="list-style-type: none"> Welding temperature of wire: 320 ± 20 °C 线材焊接温度: 320±20°C Wire welding duration: less than 3 seconds 线材焊接时长: 时长3秒以下 Can be used with dedicated connectors: 可配专用接插件使用: <ol style="list-style-type: none"> LED functional wire: red wire positive pole, black wire negative pole, LED without distinction between positive and negative poles LED功能线材: 红线正极, 黑线负极, LED不分正负极 								
5	A4				UNIT	MM	PROJECTED		PRODUCT NAME:
	A3				DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO:TP91951P6GS
	A2				DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
	A1				ROCPU TECHNOLOGY CO.,LTD				
	REV	DATE	REVISION	DESCRIPTION					
		A	B	C	D	E	F	G	





COMMON TOLERANCE

X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission

NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注
1	Base 底座	PA46	1	Silvering 镀银
2	Housing 外壳	SUS 不锈钢	1	
3	Oring O型圈	Silica gel 硅胶	1	
4	Arm nut 固定螺帽	Brass 黄铜	1	nickeling 镀镍
5	LED Base LED基座	PC 塑料	1	
6	LEDpin LED脚	Brass 黄铜	1	Silvering 镀银
7	luminous zone 发光区	PC 塑料	1	
8				
9				
10				

材质参数

A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3					X.XX	± 0.10	DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91951P6GS
A2					X.X	± 0.15	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					X	± 0.25	ROCPCU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR					