



A		B		C		D		E	
REV.	DESCRIPTION				ECN NO.	NAME		DATE	

1  
2  
3  
4  
5





### SPECIFICATIONS



Current Rating: 1.5 Amps  
 Insulation Resistance: 1000MΩ, Min  
 Contact Resistance: 20mΩ, Max  
 Withstanding Voltage: AC 500V  
 Operation Temperature: -40°to+105°  
 Contact Material: Brass  
 Standard: PA6T  
 Insrlator Material: Polyester(UL 94V-0)  
 Contact Plating: Gold Flash  
 Max.Processing Temp: 240°C for30-60seconds  
 (260°C for5seconds)



RECOMMEND P.C.B LAYOUT  
 PCB TOLERANCE:±0.05 (TOP VIEW)



P/N	PIN	DIM.A	DIM.B
2.0JN-2-03-Z	2*3	4.00	6.00
2.0JN-2-04-Z	2*4	6.00	8.00
2.0JN-2-05-Z	2*5	8.00	10.00
2.0JN-2-06-Z	2*6	10.00	12.00
2.0JN-2-07-Z	2*7	12.00	14.00
2.0JN-2-08-Z	2*8	14.00	16.00
2.0JN-2-09-Z	2*9	16.00	18.00
2.0JN-2-10-Z	2*10	18.00	20.00
2.0JN-2-11-Z	2*11	20.00	22.00
.....	....	.....	.....
2.0JN-2-35-Z	2*35	PIN-2.00	PIN

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD				 	
DIM.	TOL.	TITLE: 2.0DC3-nPin H5.7 180度 PC2.8 L8.0 6T					
x.	±0.30	DWG. NO.: 2.0JN-2-X-Z		CHECKED: MAX			
x.x	±0.20	PART NO.: 2.0JN-2-X-Z		DRAWN: ELLA			
x.xx	±0.10	UNIT: mm		SCALE: none	SHEET: 1 of 1		
GENERAL ANGLE:		DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL			
x°	±5'						
x.x°	±1'						
x.xx°	±0.5'						